

# neuma machine comparison



## neuma4

## modus

## MACRO

- ✓ 3 STROKE LENGTHS
- ✓ 4 STROKE PROFILES
- ✓ OPTIMIZED FOR BATTERIES
- ✓ 6.8 mNm TORQUE
- ✓ USER CHANGEABLE
- ✓ LOW CENTER OF GRAVITY
- ✓ 7MM RANGE OF ADJUSTMENT

- ✓ 3 STROKE LENGTHS
- ✓ 4 STROKE PROFILES
- ✓ OPTIMIZED FOR BATTERIES
- ✓ 6.8 mNm TORQUE
- ✓ USER CHANGEABLE
- ✓ LOW CENTER OF GRAVITY
- ✓ 9MM RANGE OF ADJUSTMENT
- ✓ OVERSIZED ADJUSTER
- ✓ ENLARGED RCA OPENING
- ✓ COMPATIBLE WITH N4, MACRO
- ✓ OVERSIZED THUMB GROOVES
- ✓ CARTRIDGE/ERGO ALIGNMENT
- ✓ IMPROVED GRIP PROFILES

- ✓ 3 STROKE LENGTHS
- ✓ 4 STROKE PROFILES
- ✓ OPTIMIZED FOR BATTERIES
- ✓ 10 mNm TORQUE
- ✓ USER CHANGEABLE
- ✓ LOW CENTER OF GRAVITY
- ✓ 9MM RANGE OF ADJUSTMENT
- ✓ OVERSIZED ADJUSTER
- ✓ ENLARGED RCA OPENING
- ✓ COMPATIBLE WITH N4, MACRO
- ✓ OVERSIZED THUMB GROOVES
- ✓ CARTRIDGE/ERGO ALIGNMENT
- ✓ IMPROVED GRIP PROFILES
- ✓ 50% MORE TORQUE
- ✓ HIGH TORQUE AT HIGH SPEEDS
- ✓ OVERSIZE NEEDLE PUSHER
- ✓ STANDARD STEEL HOUSING
- ✓ LASER-WELDED HOUSING/PIN
- ✓ OUR MOST ROBUST MACHINE